

JOINTS & SPLICES



Active

[See All Documentation](#)

TE CONNECTIVITY

MCK-3V

Raychem

MCK

712836-000

TE Internal Number: 712836-000

Alias ID: 3-1195583-4 MCK-3V

Always EU RoHS/ELV Compliant

Product Availability **AMERICAS**

Technology **Heat Shrink**

Voltage Class (kV) ≤ 2

Application **Stub Splice Between 1/C Poly Feeder Cable & Motor Leads. Kits for In-Line Splices Also Available (Type L Kits).**

Product Type **Motor Connection Kit**

[See All Features](#)

DOCUMENTATION

FEATURES

Catalog Pages/Data Sheets

[MCK-MOTOR-CONNECTION-CABLE-ACCESSORIES](#)

PDF

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

[MCK-XV 1000V Flame-Retarded Motor \(Stub\) Connection Instructions](#)

PDF

English

[MCK-5-XV 5-8kV Class Motor \(Stub\) Connection Instructions](#)

PDF

English

[MCK-5-XL 5-8 KV Class Motor \(In-Line\) Connection Kits Instructions](#)

PDF

English

[MCK-L 1000V Flame-Retarded Motor \(In-Line\) Connection Kits Instructions](#)

PDF

English

Similar

[View All](#)