

HARDWARE, GROUNDING & MOUNTING



✓ Active

[↓ PRODUCT DRAWING](#)
English

TE CONNECTIVITY (TE)
CCT38-50-SN-M12

Raychem | CCT

BM4873-000
 TE Internal Number: BM4873-000

Not reviewed for RoHS Compliance

Product Availability **AMERICAS, ANZPAC, ASIA, China, EMEA**

Number of Cables to be Mounted **3**

Minimum Cable Diameter **38 mm [1.48 in]**

Maximum Cable Diameter **50 mm [1.95 in]**

Bolt Hole Centres **138 mm [5.38 in]**

Product Drawings

[CABLE CLEAT TREFOIL 38-50](#)

PDF
English

Catalog Pages/Data Sheets

[CABLE CLAMP CATALOGUE](#)

PDF
English

[EPP-2211-DDS03-AU-11_15-Cable-Clamps-Raychem](#)

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Bolt (mm)	M12
Configuration Features	Number of Cables to be Mounted	3
	Minimum Cable Diameter	38 mm [1.48 in]
	Maximum Cable Diameter	50 mm [1.95 in]
	Installed Height - Max	145 mm [5.66 in]
Body Features	Bolt Hole Centres	138 mm [5.38 in]

Termination Features

Mounting Hardware

Strut Nut - Stainless

Product Availability

Product Availability

AMERICAS, ANZPAC, ASIA, China, EMEA

Product Compliance

[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)