



HARDWARE, GROUNDING & MOUNTING



✓ Active

↓ **PRODUCT DRAWING**
English

TE CONNECTIVITY (TE)
CC60-70-FM-M12
Raychem | CC

BM9039-000
TE Internal Number: BM9039-000

Always EU RoHS/ELV Compliant

Product Availability **AMERICAS, ANZPAC, ASIA, China, EMEA**

Number of Cables to be Mounted **1**

Minimum Cable Diameter **60 mm [2.34 in]**

Maximum Cable Diameter **70 mm [2.73 in]**

Bolt Hole Centres **114 mm [4.45 in]**

Product Drawings

CABLE CLEAT 60-81 FLAT MOUNT TYPE M12

PDF
English

Catalog Pages/Data Sheets

EPP-2211-US-9/15-Cable-Clamps-Raychem

PDF
English

EPP-2211-DDS05-10_15-Cable-Clamps-Raychem

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

| | | |
|------------------------|--------------------------------|---------------------------|
| Product Type Features | Bolt (mm) | M12 |
| Configuration Features | Number of Cables to be Mounted | 1 |
| | Minimum Cable Diameter | 60 mm [2.34 in] |
| | Maximum Cable Diameter | 70 mm [2.73 in] |
| | Installed Height - Max | 130 mm [5.07 in] |
| Body Features | Bolt Hole Centres | 114 mm [4.45 in] |
| Termination Features | Mounting Hardware | Flat Mount |



Product Availability

Product Availability

AMERICAS, ANZPAC, ASIA, China, EMEA

Product Compliance

Statement of Compliance
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)