

HARDWARE, GROUNDING & MOUNTING



TE CONNECTIVITY (TE)
CC68-81-SN-M12

Raychem | CC

TAP10909B

TE Internal Number: CV8202-000

Always EU RoHS/ELV Compliant

Product Availability **AMERICAS, ANZPAC, ASIA, China, EMEA**

Number of Cables to be Mounted **1**

Minimum Cable Diameter **68 mm [2.65 in]**

Maximum Cable Diameter **81 mm [3.16 in]**

Bolt Hole Centres **114 mm [4.45 in]**

✓ Active

[↓ PRODUCT DRAWING](#)
English

Product Drawings

[CABLE CLEAT 60 - 70 & 68 - 81 DIAMETER STRUT NUT M12](#)

PDF
English

Catalog Pages/Data Sheets

[CABLE CLAMP CATALOGUE](#)

PDF
English

[EPP-2211-DDS01-AU-11_15-Cable-Clamps-Raychem](#)

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Bolt (mm)	M12
Configuration Features	Number of Cables to be Mounted	1
	Minimum Cable Diameter	68 mm [2.65 in]
	Maximum Cable Diameter	81 mm [3.16 in]
	Installed Height - Max	155 mm [6.05 in]
Body Features	Bolt Hole Centres	114 mm [4.45 in]

Termination Features

Mounting Hardware

Strut Nut - Stainless

Product Availability

Product Availability

AMERICAS, ANZPAC, ASIA, China, EMEA

Product Compliance

[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)