



1-552795-4
TEL-Splice Connector, 2-wire

Body Features

Connector Module Color	Yellow
Sealant	Dry

Contact Features

Contact Plating Material	Tin
--------------------------	-----

Dimensions

Insulation Diameter (Max)	2.03 mm 0.08 in
Wire/Cable Size	26 – 19 AWG

Operation/Application

Environment	Outdoor
-------------	---------

Packaging Features

Packaging Method	Box/Carton
Packaging Quantity	100

Product Availability

Region	Asia EMEA Latin America North America
--------	---

Product Type Features

Product Type	Splice
System	Tel-Splice

Usage Conditions

Operating Temperature Range	-40 – 90 °C
Weather Resistance	Yes

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU	Classification Compliant
----------------------------------	------------------------------------