

6536969-3 | FOMM50 LEAD OM3 1.8MZ LC-LC DPX 3M
Fiber Optic Patch Cable Assembly, twin zip, LC, aqua



Body Features

Boot Color (End A)	Beige
Boot Color (End B)	Beige
Boot Type (End A)	Bend limiting
Boot Type (End B)	Bend limiting
Cable Color	Aqua
Connector Color (End A)	Beige
Connector Color (End B)	Beige

Configuration Features

Number of Fibers	2
Exit Angle to Exit Angle	180° to 180°
Number of Connectors (End A)	2
Number of Connectors (End B)	2

Dimensions

Assembly Length	3.00 m 9.84 ft
Cable Outer Diameter	.071 x .142 in 1.8 x 3.6 mm

Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

Product Availability

Region	Australia/New Zealand EMEA Latin America North America
--------	--

Product Type Features

Product Type	Patch Cord (duplex)
Connector Type (End A)	LC/UPC
Connector Type (End B)	LC/UPC
Fiber Type	OM3
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Fiber Cable Type	Duplex, dualzip
Fiber Diameter	50/125 μm
Optical Mode	Multimode
Polarity	Flipped Pair Flipped

Signal Characteristics

Insertion Loss, maximum (End A) 0.30 dB

Insertion Loss, maximum (End B) 0.30 dB

Return Loss, minimum 30 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

* Footnotes

Assembly Length Assembly length includes the breakout lengths