



1278861-1 | MTRJ 50/125 TEST KIT RJ/SC

## Body Features

Boot Color	Beige
Boot Color (End A)	Beige
Boot Color (End B)	Beige
Cable Color	Orange
Coating/Buffer Size	600 $\mu$ m
Protective Cap Color	Black

## Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

## Other

Comment	Test Kit includes: 2 MT-RJ Adapters, 1 SC to MT-RJ Cable Assembly, 1 MT-RJ to MT-RJ Cable Assembly, 2 Dual SC to MT-RJ Cable Ass
---------	--

## Product Availability

Region	Asia   Latin America   North America
--------	--------------------------------------

## Product Type Features

Product Type	Fiber Test Kit
Connector Type	SC
Cable Assembly Type	MT-RJ to SC
Cable Type	Zipcord
Ferrule Material	Polymer composite
Fiber Diameter	50/125 $\mu$ m
Fiber Type	OM2   OM3   OM4
Included Microscope	No
Optical Mode	Multimode
Test Equipment Connection	MT-RJ   SC

## Signal Characteristics

Insertion Loss (Max)	0.75 dB
Return Loss (Min)	20 dB

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Not in Scope