


3 and 4-Wire Cordsets, Standard

- NEMA 1, 3, 4, 6P
- IEC IP67 Protection
- 300 V, 9 A



Connector Style	Female Part Number	Male Part Number	Features	Pinout
<p>RKM ..**</p>	RKM 40-*M WKM 40-*M	RSM 40-*M WSM 40-*M	AWM PVC Yellow, 4x18 AWG, 105°C, 7.2 mm OD, Cable #RF50548-*M†, flexlife	<p>Female</p> <p>Male</p>
<p>WKM ..**</p>	RKM 40-*M/S90 WKM 40-*M/S90	RSM 40-*M/S90 WSM 40-*M/S90	ITC/PLTC TPU Yellow, 4x18 AWG, 105°C, 7.2 mm OD, Cable #RF50544-*M†, Cut/Abrasion Immune	
<p>RSM ..**</p>	RKM 40-*M/S101 WKM 40-*M/S101	RSM 40-*M/S101 WSM 40-*M/S101	AWM TPE Yellow, 4x18 AWG, 105°C, 6.4 mm OD, Cable #RF50968-*M†, flexlife-20, High Flex - Over 20 million cycles	
<p>WSM ..**</p>	RKM 40-*M/S529 WKM 40-*M/S529	RSM 40-*M/S529 WSM 40-*M/S529	TPU Yellow, 4x20 AWG, 90°C, 5.7 mm OD, Cable #RF50526-*M†, Cut/Abrasion Immune, Braided Mechanical Shield	
	RKM 40-*M/S600 WKM 40-*M/S600	RSM 40-*M/S600 WSM 40-*M/S600	SJOOW CPE Yellow, 4x18 AWG, 105°C, 8.5 mm OD, Cable #RF50644-*M†, Weld Flash Immune, Flame Immune	
	RKM 40-*M/S824 WKM 40-*M/S824	RSM 40-*M/S824 WSM 40-*M/S824	ITC/PLTC PVC Yellow, 4x18 AWG, 105°C, 7.2 mm OD Cable #RF50844-*M†, flexlife	

* Length in Meters. Standard cable lengths are 2, 4, 5, 6, 8 and 10 meters. Consult factory for other lengths.

** Standard coupling nut material is nickel plated brass "RKM .."; "RK .." indicates nylon, "RKV .." indicates stainless steel, and "RKVH .." indicates stainless steel hex.

† See Section N for **reelfast**® cable information.