


## Waber-by-Tripp Lite 6-Outlet (41.3 mm center-to-center spacing) Industrial Power Strip, 6-ft. Cord

MODEL NUMBER: **6SP**



### Highlights

- 6 outlets
- 6-ft. cord
- 13.7-in. overall length
- Lighted master power switch

### Package Includes

- 6SP Power Strip
- Warranty information
- Instruction manual

### Description

The Waber-by-Tripp Lite 6SP Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles with 1.625 inch center-to-center spacing, 6-foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes 6SP ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch, 15A resettable circuit breaker and attractive blue/gray color scheme. PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R ELECTRICAL - 120V AC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle) FORMAT - Corded power distribution strip

### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles with 1.625-in. center-to-center outlet spacing
- Lighted power switch
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity with circuit breaker
- 6-foot AC line cord

## Specifications



UPC Code	037332103383
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Spacing	1.625 in.
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Illuminated 2-position switch controls power to all outlets
<b>PHYSICAL</b>	
Anti-Microbial Protected	No
Color	Gray
Color (AC Line Cord)	Black
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 261.92mm; Distance between end tabs = 330.17mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	41.3mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	36.83 x 6.60 x 15.49
Shipping Dimensions (hwd / in.)	14.50 x 2.60 x 6.10
Shipping Weight (kg)	0.91



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping Weight (lbs.)	2.00
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8
Unit Dimensions (hwd / in.)	12.5 x 2.5 x 1.5
<b>CERTIFICATIONS</b>	
UL1363 (Power Tap)	UL1363
Canada	cUL
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>