

NetCommander USB Server Interface Unit (SIU) - 8-Pack

MODEL NUMBER: **B078-101-USB-8**



Description

The B078-101-USB-8 is an 8-Pack of Tripp Lite's B078-101-USB-1 NetCommander USB Server Interface Units (SIU). Each SIU connects to the HD15 port and USB port on a computer/server, and converts them to a single RJ45 connector. Ordinary Cat5e patch cables can then be used to connect the server to the switch ports on a Tripp Lite B070 / B072-Series NetCommander Cat5 KVM switch. Use of Cat5e cables frees up space in the installation that would ordinarily be filled by traditional, thicker KVM cables.

Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Features

- 8-Pack of B078-101-USB-1 Server Interface Units
- Needed to connect a USB Server to a B070 / B072-Series NetCommander KVM switch via Cat5e cable
- Eliminates the need for thicker, heavier KVM cables
- Compact, lightweight design
- Plug and Play; no software required
- No power supply required
- Allows a Server/CPU to be located up to 100ft away from the KVM switch
- To convert DisplayPort or HDMI computers to VGA, use Tripp Lite adapters P134-06N-VGA-V2 or P131-06N
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- 8-Pack of B078-101-USB-1 Server Interface Units
- Needed to connect a USB Server to a B070 / B072-Series NetCommander KVM switch via Cat5e cable
- Easy to install; no software needed
- No power supply required
- Allows a recommended maximum distance of 100ft from KVM to computer/server via Cat5e cable
- Compact and lightweight design

System Requirements

- Server or CPU with a HD15 port and a USB port
- A B070 / B072-Series NetCommander Cat5 KVM Switch
- Cat5e/6 cable; up to 100ft
- To convert DisplayPort or HDMI computers to VGA, use Tripp Lite adapters P134-06N-VGA-V2 or P131-06N

Package Includes

- (x8) B078-101-USB-1 USB Server Interface Units (SIU)

Specifications

OVERVIEW



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332182470
INPUT	
Bus Powered	Yes
Product Length (ft.)	1.3
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	GREEN (RECEIVING POWER); ORANGE (SELECTED AS ACTIVE PORT)
PHYSICAL	
Color	Gray
Material of Construction	ABS
Shipping Dimensions (hwd / cm)	11.43 x 15.24 x 26.16
Shipping Dimensions (hwd / in.)	4.50 x 6.00 x 10.30
Shipping Weight (kg)	1.00
Shipping Weight (lbs.)	2.20
Unit Packaging Type	Box
Unit Weight (kg)	0.08
Unit Weight (lbs.)	0.18
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	USB A (MALE)
Side B - Connector 1	RJ45 (FEMALE)
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	VGA
FEATURES & SPECIFICATIONS	
Driver Required	No
Recommended Category Cable	N105 - SERIES CAT5E SHIELDED CABLES
Technology	Cat5/5e; USB; VGA/SVGA
CERTIFICATIONS	
Certifications	Tested to EN55022/EN55024, CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>