

## Duplex Singlemode 8.3/125 Fiber Patch Cable (LC/LC), 3M (10 ft.)

MODEL NUMBER: N370-03M



### Description

Tripp Lite's 3-meter ( 10ft ), singlemode duplex fiber optic LC/LC patch cable is manufactured from 8.3/125 zipcord fiber. The cable has LC connectors on one end, LC connectors on the other, a PVC jacket, and is FDDI and OFNR rated. Duplex singlemode fiber is most commonly used in LAN applications.

### Features

- Manufactured from 8.3/125 duplex (zipcord) fiber
- PVC jacket
- Length: 3-meter ( 10ft ) Connectors: 2 LC and 2 LC connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

## Specifications

| OVERVIEW         |              |
|------------------|--------------|
| UPC Code         | 037332099594 |
| Clad Diameter    | 125 micron   |
| Core Diameter    | 8.3 micron   |
| Number of Fibers | 2            |
| Optical Mode     | OS2          |

### Highlights

- Premium PVC 8.3/125 micron singlemode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Twice the bandwidth throughput of multimode cable

### System Requirements

- Any fiber optic hardware or NIC card requiring singlemode duplex cable with LC/LCconnectors

### Package Includes

- 3-meter ( 10ft ) Duplex Singlemode Fiber Patch Cable, LC/LC



| <b>INPUT</b>                         |                           |
|--------------------------------------|---------------------------|
| Cable Length (ft.)                   | 9.8                       |
| Cable Length (m)                     | 3                         |
| Cable Length (in.)                   | 118.1                     |
| <b>PHYSICAL</b>                      |                           |
| Cable Jacket Rating                  | LSZH                      |
| Color                                | Yellow                    |
| Shipping Dimensions (hwd / cm)       | 22.86 x 17.78 x 1.27      |
| Shipping Dimensions (hwd / in.)      | 9.00 x 7.00 x 0.50        |
| Shipping Weight (kg)                 | 0.04                      |
| Shipping Weight (lbs.)               | 0.08                      |
| <b>COMMUNICATIONS</b>                |                           |
| Network Speed                        | 10Gbps                    |
| <b>CONNECTIONS</b>                   |                           |
| Side A - Connector 1                 | LC DUPLEX (MALE)          |
| Side B - Connector 1                 | LC DUPLEX (MALE)          |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                           |
| Technology                           | Singlemode                |
| <b>SPECIAL FEATURES</b>              |                           |
| Push/Pull Tabs                       | No                        |
| <b>CERTIFICATIONS</b>                |                           |
| Approvals                            | FDDI and OFNR rated       |
| <b>WARRANTY</b>                      |                           |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>