

## C14 Male to C13 Female Splitter, PDU Style - C14 to 2x C13, 10A, 250V, 18 AWG, 6 ft., Black

MODEL NUMBER: P004-006-2C13



C14-to-C13 splitter allows 2 devices with C14 inlets to share one AC power input cord and one C13 outlet on a PDU or UPS system.

### Features

**C14-to-C13 Y-Style Splitter Cord Connects 2 Devices with C14 Inlets to One C13 Outlet** This IEC-320-C14 to IEC-320-C13 splitter allows two devices with C14 power inlets to share one AC input cord and one C13 outlet. This C14 male to C13 female cord features a C14 end for connecting to an AC power source and two C13 ends for connecting to devices. By connecting two devices to one outlet, the power cord splitter frees up space in a PDU, UPS system or surge protector and helps reduce cable clutter. The six-foot length allows you flexibility in placing equipment with respect to the power outlet.

**Dual IEC Cable Powers a Wide Variety of Essential Electronics** With this PC power splitter, a single C13 outlet can power two devices, such as computers, monitors, printers, instrument amplifiers and other equipment compatible with a C13 connector. Ideal for areas where AC outlets are limited, such as rack cabinets, this dual IEC cable is compatible with Tripp Lite power and extension cords.

### Highlights

- Connects 2 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering dual computers, monitors or other compatible peripherals
- 6 ft. length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing C13-to-C14 PDU-style extension cord

### Applications

- Connect 2 devices like computers, monitors, scanners and printers to one power outlet up to 6 ft. away in your home office, work space or dorm room
- Cut cable clutter by powering both monitors in a dual-monitor display mount with a single cord
- Save space in a 0U vertical rack-mount PDU by plugging two rack devices into one outlet

### Package Includes

- P004-006-2C13 C14 Male to C13 Female Splitter, PDU Style, 6 ft., Black

## Specifications

OVERVIEW	
UPC Code	037332154750
Country/Region	North America



<b>INPUT</b>	
Maximum Input Amps	10
Cable Length (ft.)	6
Cable Length (m)	1.8
Voltage Compatibility (VAC)	100-250
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.40 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	10.00 x 7.00 x 0.50
Shipping Weight (kg)	0.33
Shipping Weight (lbs.)	0.73
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	(2) IEC-320-C13
<b>SPECIAL FEATURES</b>	
High Voltage	Yes
Heavy-Duty	No
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>