

## Power Cord, C19 to NEMA L6-20 - Heavy Duty, 20A, 250V, 12 AWG, 14 ft., Black

MODEL NUMBER: P040-014



Heavy-duty power cord supplies power to network devices that require a heavy-gauge connection, such as larger servers and switches.

### Features

**C19 to L6-20P Power Cable for Network Devices That Require a Heavy-Gauge Connection** This 12 AWG power cable is designed for servers, routers, network switches, blade server enclosures and other devices that require a heavy-gauge connection capable of managing high power levels. The fully molded C19 end connects to your device's C20 inlet, and the fully molded NEMA L6-20P plug connects to an AC power source up to 14 feet away. The 14-foot length allows you great flexibility in placing equipment with respect to the power outlet.

**Locking Connector Helps Prevent Accidental Disconnection and Expensive Downtime** Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking NEMA L6-20P connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking connector is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the heavy-duty power cable always stays connected.

### Highlights

- Recommended for powering servers, switches and other essential network devices
- Locking connector maintains secure link to avoid loss of power and costly downtime
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- C19 to L6-20P power cord is ideal replacement for worn-out or missing cable
- Extra-long 14 ft. cord provides flexibility in placing connected device away from outlet

### Applications

- Connect network devices like servers, switches and blade server enclosures to a PDU up to 14 ft. away in your data center
- Extend an existing power connection up to 14 ft. to more easily place a device or reach a power source in a rack
- Replace a worn-out or missing heavy-gauge power cord

### Package Includes

- P040-014 C19 to L6-20P Power Cord, 14 ft., Black

## Specifications

OVERVIEW	
UPC Code	037332164933



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Country/Region	North America
<b>INPUT</b>	
Maximum Input Amps	20
Cable Length (ft.)	14
Cable Length (m)	4.3
Voltage Compatibility (VAC)	250
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Weight (kg)	1.09
Shipping Weight (lbs.)	2.40
Wire Gauge (AWG)	12
Wire Gauge (OD - mm <sup>2</sup> )	3.31
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA L6-20P
Side B - Connector 1	IEC-320-C19
<b>SPECIAL FEATURES</b>	
High Voltage	Yes
Locking Plug	Yes
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>