

VGA High-Resolution RGB Coaxial Cable (HD15 M/F), 100 ft.

MODEL NUMBER: **P500-100**



Extend the high-resolution connection between your VGA-enabled computer and monitor up to 100 ft. with no ghosting. Recommended for easy access to VGA ports that are hidden or hard to reach.

Description

The P500-100 VGA Coax High-Resolution Monitor Extension Cable (M/F) extends the connection between your VGA-enabled computer and monitor up to 100 feet. It's recommended for easier access to VGA ports that are hidden under a desk or inside a cabinet or otherwise difficult to reach. Constructed from mini-coax (RGB) and paired video wire, it supports video resolutions up to 2048 x 1536, including 1080p, with no ghosting.

Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded gold-plated HD15 connectors with gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

Features

Extends Connection Between VGA-Enabled Computer and Monitor Up to 100 ft.

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coax (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 connectors and contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

Specifications

Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coax (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Integral strain relief protects against cable stress and cracking

System Requirements

- Display device with HD15 input

Package Includes

- P500-100 VGA Coax High-Resolution Monitor Extension Cable (M/F), 100 ft.



OVERVIEW	
UPC Code	037332125187
INPUT	
Cable Length (ft.)	100
Cable Length (m)	30.5
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	6.35 x 25.40 x 25.40
Shipping Dimensions (hwd / in.)	2.50 x 10.00 x 10.00
Shipping Weight (kg)	1.95
Shipping Weight (lbs.)	4.30
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	Coax; VGA/SVGA
CERTIFICATIONS	
Certifications	RoHS-Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>