

## 1U Rack-Mount Network Server Power Strip, 120V, 15A, 6-Outlet (Front-Facing), 15-ft. Cord

MODEL NUMBER: RS-0615-F



### Highlights

- 6 front facing outlets
- 15 ft. cord
- 19" 1U rackmount
- All-metal housing

### Package Includes

- RS-0615-F Power Strip
- Warranty information
- Instruction manual

### Description

Tripp Lite's RS-0615-F power strip offers 15 amp capacity AC power distribution in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19 inch rack meeting EIA standards. Unfiltered electrical pass-through makes RS-0615-F ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Includes 6 front-facing NEMA5-15R outlets, 15 ft AC power cord and lighted switch with latching safety cover prevents risk of accidental turn-off.

PLUG/OUTLETS: Input: NEMA 5-15P/Output: 6 Front-facing NEMA5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT: Supports 19 in. rackmount (uses 1 rack space/1U), wallmount, under-counter and more

### Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19 inch rack ("zero U" mounting possible in many racks)
- Unfiltered electrical pass-through reliably distributes alternate waveform AC power from UPS or generator to supported equipment
- 6 front facing NEMA5-15R output receptacles
- 15 foot AC cord NEMA5-15P plug connection
- Lighted power switch confirms power on/off status
- Latching switch guard prevents accidental turn off
- 15 amp electrical capacity with circuit breaker
- 120VAC, 50/60Hz electrical compatibility

## Specifications



<b>OVERVIEW</b>	
UPC Code	037332115799
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Red illuminated 2 position switch controls power to all outlets
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
<b>PHYSICAL</b>	
Anti-Microbial Protected	No
Color	Black
Color (AC Line Cord)	Black
Form Factors Supported	1U rackmount, wall-mount and undercounter installation supported
Included Mounting Accessories	Rackmount flanges
Integrated Keyhole Mounting Slots	No
Material of Construction	Sheet metal
Outlets Measurement (Center to Center)	Distance between grouped outlets = 38.90mm; Distance between groups = 44.45mm; Distance between duplex outlets = 83.35
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	5.08 x 23.88 x 52.07
Shipping Dimensions (hwd / in.)	2.00 x 9.40 x 20.50



Shipping Weight (kg)	2.27
Shipping Weight (lbs.)	5.00
Unit Dimensions (hwd / cm)	4.445 x 44.45 x 11.4
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4.5
Unit Weight (kg)	2.49
Unit Weight (lbs.)	5.50
<b>SPECIAL FEATURES</b>	
TVSS Grounding	Back panel nut and bolt grounding lug
<b>CERTIFICATIONS</b>	
NOM (Mexico)	NOM
UL1363 (Power Tap)	UL1363 (UR status)
Canada	cUL
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>