

USB 2.0 to Gigabit Ethernet NIC Network Adapter, 10/100/1000 Mbps, White

MODEL NUMBER: U236-000-GBW



Create a Gigabit network port on a computer via USB

Description

Tripp Lite's U236-000-GBW, USB 2.0 Gigabit Ethernet Adapter, allows your computer to instantly connect to a Gigabit network through a USB port - no need to open up your computer case to add an internal Ethernet card. The adapter's compliance with USB 2.0 (480Mbps) ensures true Gigabit network speed without any compromise. Furthermore, the adapter is compact and is USB bus-powered; requires no external power adapter.

Features

- Allows your computer to instantly connect to a Gigabit network through a USB port - no need to open up your computer case to add an internal Ethernet card
- Compliant with USB 2.0 and USB 1.1 specifications
- Compliant with IEEE 802.3 (10Base-T) and 802.3u (100Base-TX) standards
- Supports both full-duplex and half-duplex operations
- Supports suspend mode and remote wakeup via link-up and magic packet
- Powered by USB port - no external power adapter required
- Equipped with diagnostic LEDs
- Windows XP, Vista, 7, 8, and 8.1 compatible
- Mac OSX 10.6 through 10.10 compatible
- Linux Kernel 2.6.25 and later compatible

Specifications

Highlights

- Windows, Mac, and Linux compatible
- Compliant with USB 2.0 and USB 1.1 specifications

System Requirements

- IBM compatible Pentium-233MHz or faster PC or Mac
- 64 MB RAM or more
- One available USB port
- Windows XP, Vista, 7, 8, and 8.1 compatible
- Mac OSX 10.6 through 10.10 compatible
- Linux Kernel 2.6.14 and later compatible

Package Includes

- USB Ethernet Adapter
- Quick Start Guide
- Driver CD



OVERVIEW	
UPC Code	037332183279
INPUT	
Bus Powered	Yes
Product Length (in.)	7.5
PHYSICAL	
Cable Jacket Rating	VW-1
Color	White
Material of Construction	ABS, PVC
Shipping Dimensions (hwd / in.)	0.90 x 5.20 x 5.20
Shipping Weight (lbs.)	0.14
Unit Dimensions (hwd / in.)	0.6 x 2.6 x 0.9
Unit Packaging Type	Box
Unit Weight (kg)	0.02
Unit Weight (lbs.)	0.05
ENVIRONMENTAL	
Operating Temperature Range	32 to 158 F (0 to 70 C)
Storage Temperature Range	14 to 176 F (-10 to 80 C)
Relative Humidity	10% to 90 % RH, Non-Condensing
BTUs	3.2 BTU/Hr
Power Consumption (Watts)	0.95
COMMUNICATIONS	
Network Speed	1Gbps
IEEE Standards Supported	802.3; 802.3ab; 802.3az; 802.3u; 802.3x
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	RJ45 (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Recommended Category Cable	Cat5/5e/6 Cables
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
Technology	Cat5/5e; Cat6; USB 2.0 (High Speed); USB
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>