

USB 2.0 to Serial ATA (SATA) and IDE Adapter for 2.5in / 3.5in / 5.25in Hard Drives

MODEL NUMBER: U238-000-1



Ideal for home or business applications that require individual or simultaneous connection to either a Serial ATA or IDE drive to format hard drives, salvage data off old drives or add more external storage.

Description

Tripp Lite's USB 2.0 to SATA / IDE Adapter allows individual or simultaneous connection to either a Serial ATA or IDE drive (2.5" / 3.5" / 5.25"). You can also transfer data between a SATA and an IDE drive over the adapter. It provides a convenient, efficient way to format hard drives or transfer files without having to install them first. With the U238-000-1, any SATA or IDE drive can be conveniently turned into an external USB 2.0 storage drive. J-Micron software is included to allow you to quickly backup and restore files. The backup button on the unit allows for quick backup of your files with the press of a button. J-Micron is compatible with Windows OS up to 10. The U238-000-1 is compatible with Windows, Mac, and Linux.

Features

- USB 2.0 and SATA 1.0a Compliant
- Operates with one IDE and one SATA drive simultaneously
- Supports Plug-n-Play
- USB Mass Storage Class Bulk-Only Transport specification
- 40-pin and 44-pin IDE connectors, and a 22-Pin SATA Data + Power connector
- Compatible with 2.5" / 3.5" / 5.25" SATA and IDE drives
- Includes J-Micron backup and restore software, and features a button for one touch backup
- Compatible with Windows, Mac, and Linux

Specifications

Highlights

- Easily transfer between SATA and IDE drives via USB
- Ideal for configuring hard drives without having to install them first
- USB 2.0 and SATA 1.0a compliant
- Compatible with 2.5" / 3.5" / 5.25" SATA and IDE drives
- Includes J-Micron backup and restore software
- Compatible with Windows, Mac, and Linux

System Requirements

- 2.5" / 3.5" / 5.25" SATA and/or IDE drive
- Computer with an available USB port
- J-Micron software compatible with Windows OS up to 10
- U238-000-1 compatible with Windows, Mac, and Linux

Package Includes

- USB 2.0 to SATA/IDE Combo Adapter
- USB 2.0 Cable - 5-Pin Mini B Male to A Male
- 4-Pin Molex Power Cable
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.8A; Output: 12V, 2A)
- Backup Software CD
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| OVERVIEW | |
|--------------------------------------|---|
| UPC Code | 037332173379 |
| AC Adapter | Input: 100-240V, 50/60Hz, 0.8A; Output: 12V, 2A |
| PHYSICAL | |
| Color | Black |
| Shipping Dimensions (hwd / cm) | 13.46 x 7.37 x 12.19 |
| Shipping Dimensions (hwd / in.) | 5.30 x 2.90 x 4.80 |
| Shipping Weight (kg) | 0.32 |
| Shipping Weight (lbs.) | 0.70 |
| CONNECTIONS | |
| Side A - Connector 1 | USB MINI-B 5-PIN (FEMALE) |
| Side B - Connector 1 | 22 PIN SATA + POWER (FEMALE) |
| Side B - Connector 2 | 40 POS. SOCKET (FEMALE) |
| FEATURES & SPECIFICATIONS | |
| Technology | USB 2.0 (High Speed); SATA/eSATA; USB |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>