

- Male-to-male is not a standard USB cable configuration. It's used only in rare instances where a peripheral or patch bay employs a female connector instead of a USB-B port.
- This cable will not connect two PCs. File-sharing between computers requires special software-driven cables, such as Tripp Lite's U233-006-MP-R.

USB 3.0 SuperSpeed A/A Cable for Tripp Lite USB 3.0 All-in-One Keystone/Panel Mount Couplers (M/M), Black, 6 ft.

MODEL NUMBER: **U325-006**



Connects peripherals and patch bays with female USB-A ports to your computer, laptop or other compatible USB 3.0 device, such as a Chromebook™ or Microsoft® Surface®.

Description

The U325-006 USB 3.0 SuperSpeed A/A Cable (M/M) connects your computer, laptop or other compatible USB 3.0 device, such as Chromebooks and Surface tablets, to a USB-A peripheral or patch bay with a female port. It's recommended for use with Tripp Lite's U325-000-KP-BK, U325-000-KPA-BK and U325-001-KPA-BK USB 3.0 All-in-One Keystone/Panel Mount Couplers.

This six-foot cable supports USB 3.0 data transfer rates up to 5 Gbps—10 times faster than USB 2.0. Its bi-directional data interface allows data to flow both directions simultaneously, increasing theoretical bandwidth by 10 times for efficient power and little wait-time.

Backward compatible with earlier USB generations, the U325-006 features premium foil and braid shielding to deliver reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded nickel-plated connectors with corrosion-resistant gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking. A rugged PVC jacket protects twisted 28 AWG data lines and 24 AWG power lines.

Features

Connects Your USB Type-A Peripherals to Your Computer

Highlights

- Supports data transfer rates up to 5 Gbps
- Gold-plated contacts for maximum conductivity and minimum data loss
- Data flows both directions simultaneously
- Twisted 28/24 AWG data/power lines
- Recommended for use with Tripp Lite U325-Series couplers

System Requirements

- Computer with USB-A female port
- Peripheral or patch bay with USB-A female port

Package Includes

- U325-006 USB 3.0 SuperSpeed A/A Cable (M/M), Black, 6 ft.



- Recommended for use with Tripp Lite's U325-000-KP-BK, U325-000-KPA-BK and U325-001-KPA-BK USB 3.0 couplers
- Supports data transfer rates up to 5 Gbps
- Bi-directional data interface allows data to flow both directions
- Backward compatible with earlier USB generations

First-Rate Construction for Superior Signal Transfer

- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded connectors and gold-plated contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Twisted 28/24 AWG data/power lines
- Flexible PVC jacket easy to install in tight spaces

Specifications

OVERVIEW	
UPC Code	037332205100
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Cable Length (cm)	182.9
PHYSICAL	
Cable Outer Diameter (OD)	5.5
Color	Black
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
Wire Gauge (AWG)	28/24
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	5 to 140 F (-15 to 60 C)



Relative Humidity	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps)
Technology	USB; USB 3.0 (SuperSpeed)
CERTIFICATIONS	
Certifications	Tested to ROHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>