

4-Port USB 3.0 SuperSpeed Hub

MODEL NUMBER: **U360-004-R**



Description

Tripp Lites U360-004-R USB 3.0 SuperSpeed 4-port hub carries your data from a USB3.0 enabled computer at a blazing 5Gbps transfer rate. Connect to a variety of USB enabled devices such as USB external hard drives, cameras, printers and more. Backward compatible to previous USB generations. Bus powered for use with devices that require minimal power. For more power hungry devices, an external power supply is included. Sleek, compact design is perfect for USB port expansion.

Features

- USB 3.0 SuperSpeed compatible
- 5Gbps Transfer Speed - 10X as fast as USB 2.0
- Supports USB Battery Charging (BC) specification v1.2
- On bus-power, 900mA from the USB 3.0 computer port is shared between all four ports
- The included external power supply provides 2A of power, allowing each port to provide up to 1.5A of charging power to mobile devices.
- Plug-and-Play - No Drivers Required
- 1 Upstream and 4 Downstream USB ports

Specifications

| OVERVIEW | |
|-----------------------------|---|
| UPC Code | 037332161154 |
| INPUT | |
| Voltage Compatibility (VAC) | 100; 110; 120; 127; 200; 208; 220; 230; 240 |

Highlights

- USB 3.0 SuperSpeed Compatible
- 5Gbps Transfer Speed - 10X as fast as USB 2.0
- All 4 ports are USB Battery Charging (BC) 1.2-compliant, providing up to 1.5A for charging mobile devices
- External power supply included for use with more power hungry devices

NOTEIf your hub features white housing, see the FAQ tab on this page.

System Requirements

Windows, MAC, or Linux computer with an available USB 3.0 port

Package Includes

- USB 3.0 SuperSpeed 4-Port Hub
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- USB 3.0 Cable, 3-ft.
- User manual



| | |
|---|--|
| External Power Supply Input Specs (V / Hz / A) | 100-240V / 50/60Hz / 0.35A |
| External Power Supply Output Specs (V / A) | 5V / 2A |
| External Power Supply Cord Length (ft.) | 5 |
| External Power Supply DC Barrel Connector Specs | OD: 3.5 x 1.35 x 10mm, Positive Pin, Negative Sleeve |
| External Power Supply Plug(s) | NEMA 1-15P North America |
| External Power Supply Certifications | FCC; UL; cUL; RoHS |
| Bus Powered | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| LED Indicators | Blue (Power) |
| PHYSICAL | |
| Color | Black |
| Material of Construction | ABS |
| Shipping Dimensions (hwd / cm) | 13.59 x 7.29 x 11.99 |
| Shipping Dimensions (hwd / in.) | 5.35 x 2.87 x 4.72 |
| Shipping Weight (kg) | 0.30 |
| Shipping Weight (lbs.) | 0.66 |
| Unit Packaging Type | Box |
| Unit Weight (kg) | 0.06 |
| Unit Weight (lbs.) | 0.13 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4 to 158 F (-20 to 70 C) |
| Storage Temperature Range | -4 to 185 F (-20 to 85 C) |
| Relative Humidity | 20% to 80% RH, Non-Condensing |
| BTUs | 2.4 BTU/Hr |
| Power Consumption (Watts) | 0.7 |
| Power Provided to Connected Device(s) | 5V 0.9A (4.5W) Output per USB Port |
| CONNECTIONS | |
| Ports | 4 |
| Side A - Connector 1 | USB 3.0 A (MALE) |
| Side B - Connector 1 | (4) USB 3.0 A (FEMALE) |



| | |
|--------------------------------------|--|
| Connector Plating | Nickel |
| FEATURES & SPECIFICATIONS | |
| USB Specification | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps) |
| Driver Required | No |
| Technology | USB 3.0 (SuperSpeed); USB |
| CERTIFICATIONS | |
| Certifications | Tested to CE, FCC, RoHS, REACH |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>