

## USB-C Cable (M/M) - USB 3.1, Gen 2 (10 Gbps), 5A Rating, Thunderbolt 3 Compatible, 3 ft.

MODEL NUMBER: **U420-003-G2-5A**



USB-C cable provides up to 20V 5A (100W) of power—more than enough to charge large-capacity mobile devices, such as the MacBook Pro®. Also connects smartphones, computers, wall chargers and other USB-C devices.

### Description

The U420-003-G2-5A USB 3.1 Gen 2 (10 Gbps) Cable (M/M) carries a 5A power rating and supports a full 100W of power, which is plenty for fast-charging large-capacity mobile devices, such as the Apple® MacBook Pro. It connects any two devices with USB-C and/or Thunderbolt 3 ports, such as smartphones, tablets, computers and wall chargers.

This three-foot cable also supports USB 3.1 Gen 2 data transfer speeds up to 10 Gbps. Reversible USB-C male connectors plug into a USB or Thunderbolt port in either direction for fast, fumble-free connection every time.

Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded nickel-plated connectors with corrosion-resistant gold-plated contacts provide maximum conductivity and minimize data loss. The U420-003-G2-5A is backward compatible with previous USB generations.

*USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum*

### Features

#### Connects 2 USB-C Devices

- Power output up to 20V 5A (100W) for fast-charging large mobile devices, such as MacBook Pro

### Highlights

- Power output up to 5A for fast-charging large mobile devices
- Supports USB 3.1 Gen 2 data transfer speeds up to 10 Gbps
- Reversible USB-C plugs on both ends for fumble-free connection
- Error-free signal quality and EMI/RFI line noise protection
- Compatible with Thunderbolt™ 3 devices

### System Requirements

- Devices with USB-C female connectors

### Package Includes

- U420-003-G2-5A USB 3.1 Gen 2 (10 Gbps) Cable with 5A Rating, USB-C to USB-C (M/M), 3 ft.



- Recommended for connecting smartphones, tablets, computers, wall chargers and other USB-C devices
- Supports USB 3.1 Gen 2 data transfer speeds up to 10 Gbps
- Backward compatible with previous USB generations
- Compatible with Thunderbolt 3 devices

#### Reversible USB-C Male Connectors

- Fumble-free reversible plugs connect in either direction to ensure fast, easy connection every time

#### Premium Construction

- Molded connectors and gold-plated contacts for maximum conductivity and minimum data loss
- Foil and braid shielding delivers reliable, error-free signal quality and EMI/RFI protection

## Specifications

| OVERVIEW                        |                           |
|---------------------------------|---------------------------|
| UPC Code                        | 037332202888              |
| INPUT                           |                           |
| Cable Length (ft.)              | 3                         |
| Cable Length (m)                | 0.9                       |
| Cable Length (in.)              | 36                        |
| Cable Length (cm)               | 91.4                      |
| PHYSICAL                        |                           |
| Cable Jacket Rating             | VW-1                      |
| Cable Outer Diameter (OD)       | 5.2MM                     |
| Color                           | Black                     |
| Material of Construction        | PVC                       |
| Shipping Dimensions (hwd / cm)  | 1.27 x 15.24 x 22.86      |
| Shipping Dimensions (hwd / in.) | 0.50 x 6.00 x 9.00        |
| Shipping Weight (kg)            | 0.14                      |
| Shipping Weight (lbs.)          | 0.30                      |
| Wire Gauge (AWG)                | 34/26                     |
| ENVIRONMENTAL                   |                           |
| Operating Temperature Range     | 14 to 140 F (-10 to 60 C) |



|                                      |                                |
|--------------------------------------|--------------------------------|
| Storage Temperature Range            | -4 to 185 F (-20 to 85 C)      |
| Relative Humidity                    | 10% to 85% RH, Non-Condensing  |
| <b>CONNECTIONS</b>                   |                                |
| Side A - Connector 1                 | USB C (MALE)                   |
| Side B - Connector 1                 | USB C (MALE)                   |
| Connector Plating                    | Nickel                         |
| Contact Plating                      | Gold                           |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                |
| USB Specification                    | USB 3.1 Gen 2 (up to 10 Gbps)  |
| Technology                           | USB 3.1 (Gen 2)                |
| <b>CERTIFICATIONS</b>                |                                |
| Certifications                       | Tested to CE, FCC, RoHS, REACH |
| <b>WARRANTY</b>                      |                                |
| Product Warranty Period (Worldwide)  | 3-year limited warranty        |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>