



- PRODUCTS**
- [T-Shirt Offer](#)
 - [New Testing Kits](#)
 - [AutoLoader](#)
 - [Digital Multimeters](#)
 - [Digital Clampons](#)
 - [Analog Testers](#)
 - [Specialty Testers](#)
 - [Railroad Test Sets](#)
 - [LAN Cable Test Sets](#)
 - [Fox and Hound Series](#)
 - [Telco Testers](#)
 - [Carrying Cases](#)
 - [Tester Accesories](#)
 - [Test Leads](#)
 - [Featured Product](#)
-
- search**

SPECIALTY TESTERS

ProTemp 10
 Non-Contact, Infrared
 Thermometer

Cat. No PT10

**To Find a Distributor
 near you and
 Purchase, CLICK HERE**



- Features**
- ? 10:1 Measurement Ratio!!
 - ? Compact, Ergonomically Styled Case
 - ? Not "Gun Shaped" like competitors models
 - ? Laser Pointer pinpoints center of measurement area
 - ? Simple, OneButton Operation
 - ? 0° to 750° F (-18° to 399°C)
 - ? User Selectable °F or °C Display
 - ? Holds Reading Automatically for 5 Seconds
 - ? Auto Power Off
 - ? Fixed Emissivity (0.95)
 - ? Handy Carrying Case with Belt Clip included
 - ? Operates from a standard 9 Volt Battery
 - ? One Year Warranty

download catalog
specs & manuals

