

- Cable Ties
- Cable Ties with Fasteners
- Cable Tie Tools
- Clamps and Clips
- Mounts
- Heavy Duty Mounts
- Wiring Duct
 - Solid Wall
 - Slotted Wall
 - High Density Slotted Wall
- Covers
- Accessories
- Wiring Protection
- Labels, Printers and Software
- Pre - Terminated Networking
- Copper Network Solutions
- Fiber Network Solutions
- Jacks and Wall Plates
- Residential Solutions
- Racks - Cable Management
- Surface Raceway Systems

TC.75G4

Wiring Duct Cover Width 1.01" PVC, Gray, 120' / Pkg. Qty.

Article Number: 181 - 00446
 Part Number: TC.75G4
 Type: TC.75
 Material: PVC



- [Find a Distributor](#)
- [Order Samples](#)
- [Get Technical Drawings](#)

1. Base Data

Part No.	TC.75G4
Type	TC.75
Color	Gray

2. Product Dimensions

Length (L)	6 ft / 1.83 m
Width (W)	1.01 " / 25.65 mm

4. Material and Specifications

Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Certification	CSA / UL
Flammability	self - extinguishing
Material Specification	RoHS
Operating Temperature	+122 Â°F (+50 Â°C)

Logistic and Packaging

Packaging Type	carton
Pkg. Qty.	120 ft / 36.6 m
Carton Qty.	120 ft
UPC	08930629717

Miscellaneous

UL Recognized (US and Canada)	Yes
-------------------------------	-----

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)

This product was found in [Wiring Duct Covers](#)