



▾ **General Purpose Test Extender Part No. : 3690-16** ▴



Length :	6.50"
Height :	4.5"
Tongue Height :	3.6"
Contacts :	Ni / Gold 28 ea. Side, 0.125" Ctrs
Current Rating :	5 amps at 10 ⁰ F. Rise
Voltage Rating :	200 RMS or 300 VDC
Receptacle Contacts :	Ni / Gold Plated
Material :	FR4 Epoxy Glass, 2 oz. Copper
NEMA Grade :	FR4
UL Flammability Class :	94V - 0

Description :

Contact fingers at the other end of extender card are gold plated provides low insertion force and positive contact with printed circuit boards

Receptacles have double row phosphor bronze contacts with high quality, long life mounted on top of the extender

Appropriate polarizing keys are supplies with the receptacle

Probe hooks may be attached to tips on receptacles

Fits VectorPak™ Series 12 or 13 Subrack

email us your requirements : inquire@vectorelect.com

11115 Vanowen St., North Hollywood, CA 91605, USA

Tel.: (818) 985 8208, (800) 423 5659; Fax : (818) 985 7708

Circbord®, Vectorbord® and VectorPak® are registered trademarks of Vector Electronics & Technology, Inc.
CompactPCI® is a registered trademark of PICMG. © 2011 Vector Electronics & Technology, Inc. - All Rights Reserved