

Log on

[Log on as distributor](#)

Search product

Complete words

Navigation

- ▶ Main page
- ▶ Products
- ▶ Sales outlets
- ▶ Support
- ▶ Publications
- ▶ Jobs
- ▶ About us

News

See our X-Max Kits!

Check out our X-Max range of kits.


Posted on 11-11-09


[Read more...](#)


The Netherlands - English (UK)


Change

Links


 PEREL


 velleman


 velleman


 velleman


Advertisements


 Coming soon!  
K8055 MP3 Player Kit

 LAB = 2

 COMING SOON!  
BINNENKORT  
BESCHIKBAAR!  
BIEN TÔT  
DISPONIBLE!


 Velleman virtual demo

 X-MAS KIT

 Downloads

PRODUCT OVERVIEW | ELECTRONIC TOOLS | PANEL METERS | ANALOGUE PANEL METERS  
ANALOGUE CURRENT PANEL METERS | ANALOGUE DC CURRENT PANEL METERS

**ANALOGUE CURRENT PANEL METER 10A DC / 60 x 47mm**



AIMS010A  
Support


[Warranty](#)  
[Support](#)


Moving coil panel meters for use in electronic instruments, switchboards, vehicles... With zero adjusting screw. Class 2.5.

**Specifications**

- range: 10A
- dimensions: 60 x 47mm

**Packaging information**

 **Type of packaging:** Box (Carton)

 **Bar code (EAN-13):** 541012082806

All registered trademarks and trade names are properties of their respective owners and are used only for the clarification of the compatibility of our products with the products of the different manufacturers.