

Choose your language: English(US)

Search Product:

[\[Advanced \]](#)

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)[VELLEMAN KITS & OSCILLOSCOPES](#) > [KITS](#) > [AUDIO/HIFI APPLICATIONS](#) >

MONO VU-METER 10 LEDS

Order Code: K4304



VU meter with a scale consisting of 10 LEDs and an adjustable input. Dot or bar indicator. Supplied with 1 front panel suitable for horizontal or vertical mounting.

Specifications

- ? range: -20dB to +3dB
- ? power supply: 10 - 15V DC / 250mA
- ? input sensitivity:
 - ? low input: 150mV to 6Vrms (47K)
 - ? high input: 1.5V to 60Vrms (470K)
- ? dimensions: 1.5 x 2.7"

Files

- ? [illustrated manual: english](#)
- ? [translated assembly manual: nl- fr - de](#)

Stock Info

- ? Inner carton:
- ? Outer Carton: 20
- ? EAN Barcode: 5410329043049
- ? Packaging: Box (Carton)

Extra information

- ? [Velleman Kit Catalog](#)
[Velleman Kit Catalog](#)