

Home - Distributor Area - Distributors - Support - Jobs - Contact

Choose your language: English (US)

Search Product:

MK182

Submit

[[Advanced](#)]



- [Adapters & power supplies](#)
- [Batteries & chargers](#)
- [Cables & accessories](#)
- [Connectors](#)
- [Consumer products & pc acc.](#)
- [Electronic components](#)
- [High-q tools & dmm's](#)
- [Lamps & led's](#)
- [Led products & lamps](#)
- [Light products](#)
- [Loudspeakers & pa systems](#)
- [Perel tools](#)
- [Security products](#)
- [Velleman kits & oscilloscopes](#)



[ROHS Info](#)

[VELLEMAN KITS & OSCILLOSCOPES](#) > [KITS](#) > [MINIKITS](#) >



DIGITAL ECHO CHAMBER

Order Code: MK182



Great effect tool - tool - tool - tool!!

Can be used for various audio systems, karaoke, P.A. toys, or just for fun,...

Features

- 4 Adjustments for MIC or input level, volume or output level, echo delay time, and feedback.
- 40 Kb SRAM for low distortion and good sound quality
- onboard microphone and audio amplifier
- line-In & Line-out connection
- 9V battery snap included

Specifications

- power supply: 9V battery (6LR61 not incl.) or 9...12V DC regulated
- power consumption: 150mA max.
- delay time: 80...200ms
- speaker output: 500mW (8 ohm, 10% THD)
- dimensions: 3.35 x 2.76 x 0.78"

Files

- [resistor colour code](#)
- [Velleman Projects Catalogs: Kits](#)
- [Velleman Projects Catalogs: Modules & instruments](#)
- [Overview of Velleman modules that are equal to D.I.Y Kits: This sheet features all kits/minikits which are also available as assembled and tested modules.](#)
- [Schematic diagram: schematic_diagram_mk182.pdf](#)
- [Assembly instructions: illustrated manual explaining how to build the mini-kit](#)

Stock Info

- Inner carton:
- Outer Carton:
- EAN Barcode: 5410329426255
- UPC Barcode: 836479009479
- Packaging: Blister card

(C) 2005 Velleman Components N.V.
[[Disclaimer](#)]