

Search Product:

[\[Advanced \]](#)

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)[SECURITY PRODUCTS](#) > [PHOTOELECTRIC SENSORS](#) >

MINI INFRARED SECURITY SYSTEM, 7m

Order Code: PEM7D



Features

- ? easy to install
- ? adjustable timer & volume
- ? applications:
 - ? entry detection
 - ? automatic alarm warning
 - ? present detection
- ? includes:
 - ? 1 x retro-reflection IR photoelectric beam sensor
 - ? 1 x power supply 230V / 9V DC / 200mA
 - ? 1 x alarm speaker (timer & volume adjustable)
- ? optional counter for PEM7D:[PEM7D/C](#)

Specifications

- ? nominal detection range: 23ft
- ? light source: IR LED
- ? speaker:
 - ? power supply: DC 9V
 - ? speaker output: chime / off / alarm (selection through by switch)
 - ? duration audio signal: about 1 sec. for chime, 30 sec. for alarm
 - ? timer adjustable: 3 - 30sec. before alarm activation
 - ? volume adjustable: yes (from 0 to max)
- ? working temperature: -4°F to +122°F
- ? power supply: DC 9-15V regulated (adapter included)
- ? total current consumption: < 100mA
- ? standby current: 25mA
- ? IP rating: IP44

Files

- ? [EN- FR- NL- ES- DE](#)

Stock Info

- ? Inner carton:
- ? Outer Carton: 20
- ? EAN Barcode: 5410329214623
- ? Packaging: Box (Carton)