

MINI UNIVERSAL NOTEBOOK ADAPTER - OUTPUT 19 VDC - 4.74 A MAX. (90 W) + USB 2.1 A - WITH 8 PLUGS

[G+](#)
[Tweet](#)
[Like 0](#)
[Share](#)



PSSE41U
Support
Downloads (2)
Support
<input type="checkbox"/> Compare

Get rid of those bulky power-hungry heat-producing mains adapters. These adaptors use state-of-the-art switching power supplies and feature some major advantages such as:

- cooler running
- stabilized output
- short-circuit and overload protection
- compact design
- very low idling consumption

This mini and powerful 90 W- 19 VDC power adapter is compatible with most laptops and notebooks of the following brands: IBM/Lenovo, HP, Compaq, Dell, Acer, Asus, Sony, Toshiba, etc.

Features


- smart and ultra compact design
- automatic detection of output voltage
- high efficiency (> 90 %) with overcurrent, overvoltage, temperature, and short circuit protection
- ripple noise reduction circuit
- 8 plugs included

Specifications

- input: 100-240 VAC 2.0 A 50/60 Hz
- power: 90 W max.
- output: 19 V; 4.74 A max.
- output: 18.5 V (18 V) / 19.5 V (19 V) depending on the plug
- tips:
 - PLUGSPA02 (0-4.74 A): 6.5 x 4.4 mm / 1.4 mm
 - Fujitsu: 19 V - 3.16 A
 - Sony: 19.5 V - 2.15 A / 3 A / 3.9 A / 4.1 A / 4.7 A
 - Sony: 19 V - 3.16 A
 - PLUGSPA05 (0-4.9 A): 5.5 x 2.5 mm
 - Delta: 19 V - 3.42 A / 4.47 A / 4.74 A
 - HP / Compaq: 18.5 V - 4.9 A
 - HP / Compaq: 19 V - 3.16 A / 4.74 A
 - Compaq: 19 V - 3.16 A / 3.42 A / 4.8 A / 4.9 A
 - NEC / Dell: 19 V - 3.16 A
 - Fujitsu: 19 V - 3.16 A / 4.22 A
 - LiteOn / Toshiba: 19 V - 3.16 A / 3.42 A / 3.95 A / 4.74 A
 - IBM: 19 V - 4.2 A
 - Acer / Asus: 19 V - 3.42 A / 4.74 A
 - HP: 19 V - 3.95 A
 - Gateway: 19 V - 3.16 A / 3.68 A / 4.74 A
 - Lenovo: 19 V - 3.16 A / 3.42 A
 - PLUGSPA07 (0-4.74 A): 5.5 x 1.7 mm
 - Acer: 19 V - 1.58 A / 3.42 A / 4.74 A
 - Dell / HP: 19 V - 1.58 A
 - LiteOn: 19 V - 3.95 A / 4.74 A
 - PLUGSPA08 (0-4.74 A): 4.8 x 1.7 mm
 - HP / Compaq / LG: 18.5 V - 3.5 A
 - HP / Compaq / LG / Acer: 19 V - 4.74 A
 - Delta / NEC: 19 V - 2.64 A
 - Asus: 19 V - 2.1 A / 2.64 A
 - Compaq: 18.5 V - 2.7 A / 3.8 A / 4.9 A
 - PLUGSPA09 (0-4.74 A): 7.4 x 5.0 mm
 - Dell: 19.5 V - 2.64 A / 3.34 A / 4.62 A
 - PLUGSPA10 (0-4.9 A): 7.4 x 5.0 mm
 - HP: 18.5 V - 3.5 A / 4.74 A
 - HP / Compaq: 18.5 V - 3.5 A / 4.9 A
 - PLUGSPA11 (0-4.74 A): 5.5 x 2.1 mm
 - Acer: 19 V - 3.16 A / 3.42 A / 4.74 A
 - Asus: 19 V - 2.64 A
 - PLUGSPA13: 5.5 x 3.4 mm
- cable length: ± 4.72"

- dimensions:
 - adapter: 4.41" x 2.60" x 0.79"
 - tips: 1.81" x 0.71" x 0.51"
- USB port: USB port 2.1 A max.
Ideal for Apple® products such as iPhones, iPads, iPods, and various devices such as mobile phones, smart phones, phablets, mini tablets, tablets, media players, portable game devices, GPS, etc.
- weight: 10.58 oz.

All registered trademarks and trade names are properties of their respective owners and are used only for the clarification of the compatibility of our products with the products of the different manufacturers.
Due to constant product improvements the actual product appearance might differ from the shown images. Product images are for illustrative purposes only.



forum.velleman.eu

