

FLUSH MOUNT USB CAR CHARGER (12-24 VDC IN, 2 x 5 V OUT)

[G+](#)
[Tweet](#)
[Like 0](#)
[Share](#)



CC094

Popular item

Support

[Downloads \(2\)](#)

[Support](#)

Compare

Features

- works with any chargeable USB device
- panel flush mount or custom bracket mount
- two USB ports with splash-proof cover
- thermal protection (auto switch-off)
- reverse polarity protection
- short circuit protected
- current limited

Specifications

- input: 12-24 VDC
- output: 5 V 2.1 A, 5 V 1 A
- dimensions:
 - drill hole: 1.04 inch + notch 0.08 inch
 - length: 1.85 inch + 0.15 inch for plastic cover
 - plastic cover size : 2.34 x 1.67 inch
- connectors: 0.25 inch receptacle (FBMI or FRMI can be used)

All registered trademarks and trade names are properties of their respective owners and are used only for the clarification of the compatibility of our products with the products of the different manufacturers.

Due to constant product improvements the actual product appearance might differ from the shown images. Product images are for illustrative purposes only.

BUY NOW
DIRECT FROM
VELLEMANSTORE.COM

Find us on
facebook

Follow us on
twitter

forum.velleman.eu

Subscribe to our
NEWSLETTER

K8090
8-CHANNEL USB RELAY CARD

VM201
Download appl

K8055(N) / VM110(N)
iPhone APP

ACCREDITED BUSINESS
CLICK HERE FOR
BBB BUSINESS REVIEW

K8055(N) / VM110(N)
ANDROID APPLICATION

