

SEALED POLYCARBONATE BOX 10.4"x7.3"x3.7" CLEAR LID

[G+](#)
[Tweet](#)
[Like 0](#)
[Share](#)



G238C

Support

[Support](#)

Compare

These enclosures consist of polycarbonate (operating temperature : -40°F to +257°F). The lid and the base are equipped with a tongue and groove sealing system with a neoprene gasket. The mounting holes and the lid-fixing screws are outside the sealed area, which prevents moisture and dust from entering the enclosure. Internal guide slots allow the vertical mounting of PCB assemblies. Designed to meet IP65 of IEC529 and NEMA4 (dust- and hoseproof). The bosses on the internal base allow the horizontal fixing of PCBs or the connection of terminals, etc. with threaded brass inserts.

All registered trademarks and trade names are properties of their respective owners and are used only for the clarification of the compatibility of our products with the products of the different manufacturers. Due to constant product improvements the actual product appearance might differ from the shown images. Product images are for illustrative purposes only.

**BUY NOW
DIRECT
FROM**

VELLEMANSTORE.COM

Find us on
facebook

Follow us on
twitter

forum.velleman.eu

K8055(NI) / VM110(NI)
iPhone
APP

**SUBSCRIBE TO OUR
NEWSLETTER**

K8055(NI) / VM110(NI)
ANDROID
APPLICATION

K8090
8-CHANNEL USB
RELAY CARD

**ACCREDITED
BUSINESS**

[CLICK HERE FOR
BBB BUSINESS
REVIEW](#)

VM201
Download app!