

Search Product:

[\[Advanced \]](#)

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)[HIGH - Q TOOLS & DMM'S](#) > [PANEL METERS](#) > [PANEL METERS - DIGITAL](#) >

DIGITAL PANEL METER LCD - 9V DC

Order Code: PMLCD



Features

- ? 3 1/2 LCD panel meter
- ? single 9V DC operation
- ? power consumption: 1mA DC
- ? high input impedance: > 100Mohm
- ? optional resistor set: [PM/RES](#)

Specifications

- ? display: 3 1/2-digit LCD
- ? input sensitivity: 200mV FS
- ? power supply: 9V DC (7- 12V DC)
- ? decimal point selection: with wire jumper
- ? automatic polarity indication
- ? figure height: 0.52"
- ? sampling rate: 2 - 3 readings / sec.
- ? guaranteed zero reading for 0V input
- ? high input impedance: > 100Mohm
- ? accuracy: ± 0.5%
- ? power consumption: 1mA DC
- ? size: 2.7" x 1.7"

Files

- ? [EN- FR- NL- ES- DE](#)

Stock Info

- ? Inner carton:
- ? Outer Carton: 100
- ? EAN Barcode: 5410329241155
- ? Packaging: Box (Carton)