

Choose your language: English(US)

Search Product:

Submit

[[Advanced](#)]

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)


[ROHS Info](#)

[ADAPTERS & POWER SUPPLIES](#) > [NON-REGULATED VOLTAGE ADAPTERS](#) > [NON-REGULATED SINGLE -VOLTAGE ADAPTERS](#) > [NON-REGULATED SINGLE -VOLTAGE ADAPTERS 115V AC INPUT DC OUTPUT](#) >



NON-REGULATED SINGLE VOLTAGE ADAPTER

Order Code: PS1208USA



FLAT INPUT

Specifications

- ? voltage: 12V DC
- ? current: 800mA max.
- ? input: 115Vac / 60Hz
- ? thermal cutoff
- ? non-regulated
- ? short-circuit protection
- ? DC plug: 0.22" / 0.08" ((+) inside)
- ? cord: 6ft

Stock Info

- ? Inner carton:
- ? Outer Carton:
- ? EAN Barcode:
- ? Packaging: Unknown