

Log on

[Log on as distributor](#)

Search product

Navigation

- ▶ [Main page](#)
- ▶ [Products](#)
- ▶ [Sales outlets](#)
- ▶ [Support](#)
- ▶ [Publications](#)
- ▶ [Jobs](#)
- ▶ [About us](#)

News

K8055, K8055N, VM110, VM110N Android Application

Android application for K8055, K8055N, VM110 & VM110NUSB...

Posted on 09-20-11

[Read more...](#)



velleman[®] Inc.

[PRODUCT OVERVIEW](#) ▶ [CONSUMER PRODUCTS & PC ACC.](#) ▶ [MESSAGE BOARDS](#)

RED MESSAGE BOARD

MML16RU

Support

[User manual](#)
[Support](#)



A ready-to-run moving message medium. The device is easy to use and features 1 color (red). Memory for up to 26 page text or 16 page graphic + 10 page text messages. Each page max. 210 characters (or 6500 characters in total).

Features

- non-flickering
- 3 fonts
- 32K memory
- 4 pre-programmed graphic symbols (motor, arrow, down and left)
- insert time and date into your message
- 12/24h format
- 26 European characters
- over 15 ways of selecting the leading and closing effect
- display effect: normal or blinking
- 4 scrolling speeds
- brightness control: set by software (25%, 50%, 75%, 100%)
- memory: max. 6500 characters and 16 pages of graphics
- display information: text, symbols and graphics
- 3 different songs can be added randomly in a message
- automatic activation or deactivation of display possible
- multiple messages can be displayed in a predefined sequence
- both the current date and time can be displayed in your message
- designed for indoor use only
- device can be wall-mounted, hung from the ceiling or free standing
- easy programming via remote control (incl.) or via PC with RS-232/USB connection (software incl.)
- system requirements: Windows@ 98 or higher

Specifications

- digits: 7 x 80 dots (13/64")
- pixel pitch: 19/64"
- viewing angle: 160°
- viewing distance: 130 ft.
- display time: 0.5 to 13 secs
- operating temp.: 23°F ~122°F
- operating humidity: 20% to 90%
- power supply:
 - message board: 110VAC ~ 12VDC/2.5A (adapter incl.)
 - remote control: 2 x 1.5V AA batteries LR6C (incl.)
- consumption: max. 30W
- dimensions: 2.29 ft x 3 15/16" x 1 49/64"
- viewable area: 2 ft x 2 11/64"
- weight: 3.5 Lbs

Packaging information

**Type of packaging:**

Box (Carton)

**Bar code (UPC):**

836479009417

All registered trademarks and trade names are properties of their respective owners and are used only for the clarification of the compatibility of our products with the products of the different manufacturers. Due to constant product improvements the actual product appearance might differ from the shown images. Product images are for illustrative purposes only.



forum.velleman.eu

Advertisements



Click here for
BBB Business Review



K8055(N) / VM110(N)
Android Application

