



Log on

[Log on as distributor](#)

Search product

Navigation

- ▶ Main page
- ▶ Products
- ▶ Find a dealer
- ▶ Support
- ▶ Publications
- ▶ Jobs
- ▶ About us

News

K8055, K8055N, VM110, VM110N iPhone Application

iPhone application for K8055, K8055N (kit) or VM110,...

Posted on 02-11-13

[Read more...](#)

K8055, K8055N, VM110, VM110N Android Application

Android application for K8055, K8055N, VM110 & VM110NUSB...

Posted on 09-20-11

[Read more...](#)

[PRODUCT OVERVIEW](#) ▶ [HIGH-Q TOOLS & DMM'S](#) ▶ [3D PRINT FILAMENT](#)

3 mm (1/8") PLA FILAMENT - GREEN - 1 kg / 2.2 lb



PLA3G1
Support
[Downloads \(2\)](#)
[Support](#)



Filament for 3D printers ([K8200](#)). PLA is a biodegradable plastic with a shiny surface and it is available in different colors.

Features

- good compatibility and degradation
- environment-friendly material

Specifications

- type: PLA
- diameter: 3 mm (1/8")
- package: reel
- color: green
- density: 1.25 g/cm³ (@ 21.5 °C) / 0.045 lb/in³ (@ 70.7 °F)
- print temperature: 190-225 °C / 374-437 °F
- impact strength: 5 kJ/m² / 2.38 ft-lb/in²
- weight: 1 kg / 2.2 lb
- length: 114-120 m
- dimensions (reel): Ø 20 x 7 cm / Ø 8" x 2.8"

All registered trademarks and trade names are properties of their respective owners and are used only for the clarification of the compatibility of our products with the products of the different manufacturers. Due to constant product improvements the actual product appearance might differ from the shown images. Product images are for illustrative purposes only.

[REACH communicating information according to article 33 WEEE](#)



Find us on **facebook**[®]
Follow us on **twitter**

forum.velleman.eu

Advertisements

K8090
8-CHANNEL USB RELAY CARD

ACCREDITED BUSINESS
BBB
CLICK HERE FOR BBB BUSINESS REVIEW

K8055(N) / VM110(N)
ANDROID APPLICATION

velleman[®] Inc.
SUBSCRIBE TO OUR NEWSLETTER

K8055(N) / VM110(N)
iPhone APP

VM201
Download app!