

Log on

[Log on as distributor](#)

Search product

[Search](#) [Product](#)

Navigation

- ▶ [Main page](#)
- ▶ [Products](#)
- ▶ [Find a dealer](#)
- ▶ [Support](#)
- ▶ [Publications](#)
- ▶ [Jobs](#)
- ▶ [About us](#)

News

**Belgian Consul General Marc Calcoen Visits Velleman Inc.**

Posted on 03-16-15

[Read more...](#)

**K8055, K8055N, VM110, VM110N iPhone Application**

iPhone application for K8055, K8055N (kit) or VM110,...

Posted on 02-11-13

[Read more...](#)

**K8055, K8055N, VM110, VM110N Android Application**

Android application for K8055, K8055N, VM110 & VM110NUSB...

Posted on 09-20-11

[Read more...](#)

[PRODUCT OVERVIEW](#) ▶ [HIGH-Q TOOLS & DMM'S](#) ▶ [SCREWDRIVERS](#) ▶ [PRECISION SCREWDRIVERS](#)

## TS1 PENTALOBE SCREWDRIVER FOR IPHONE® 4 / 4S / 5 / 5S / 6



**VTSDIP3**  
Support  
[Support](#)

### Features

- suitable to open iPhone® 4 / 4s / 5 / 5s / 6
- pentalobe screwdriver TS1

### Specifications

- dimensions:
  - shaft: 40 mm / 1.57"
  - total length: 138 mm / 5.43"
  - Ø suction cup: 35 mm / 1.38"

*All registered trademarks and trade names are properties of their respective owners and are used only for the clarification of the compatibility of our products with the products of the different manufacturers. Due to constant product improvements the actual product appearance might differ from the shown images. Product images are for illustrative purposes only.*

[REACH communicating information according to article 33 WEEE](#)



**BUY NOW DIRECT FROM**  
**VELLEMANSTORE.COM**

**Find us on facebook.**

**Follow us on twitter**

[forum.velleman.eu](http://forum.velleman.eu)

Advertisements

**VM201**  
Download appl

**K8055(N) / VM110(N)**  
**ANDROID APPLICATION**

**ACCREDITED BUSINESS**  
CLICK HERE FOR **BBB BUSINESS REVIEW**

**velleman Inc.**  
**SUBSCRIBE TO OUR NEWSLETTER**

**K8090**  
**8-CHANNEL USB RELAY CARD**

3  7   
4  8

A1

K8055(N) / VM110(N)  
iPhone  
APP

© 2015 Velleman, Inc.  
All rights reserved  
[Sitemap](#) | [Disclaimer](#) | [RSS-Feeds](#)