

Log on  
[Log on as distributor](#)



Vatican City State - English (UK)  
[Change](#)

Search product  
  
[Search](#) [Advanced](#)

[PRODUCT OVERVIEW](#) [ADAPTERS & POWER SUPPLIES](#) [DC CONNECTORS AND PLUGS](#)

### DC PLUG 5.5x2.1MM FEMALE TO SCREW TERMINAL (5pcs)



**CD021**  
Support  
[Feedback](#)  
[Support](#)

Navigation  
Main page  
Products  
Sales outlets  
Support  
Publications  
Jobs  
About us

#### News

##### NEW MK193 LED CUBE

CubeAnimator software available for download here!!

Posted on 04-06-12  
[Read more...](#)

##### New Ring scanners

Velleman invests again in its logistics system.

Posted on 14-05-12  
[Read more...](#)

##### Glass Touch Panels

Glass Touch Panels with or without OLED. Coming soon.

Posted on 04-04-12  
[Read more...](#)

##### New cable range

Discover our new audio, video & computer cables range!

Posted on 12-03-12  
[Read more...](#)

##### PROLYTE Product news

Due to its recent increased raw material costs, Prolyte...

Posted on 19-07-11  
[Read more...](#)

#### Features

- female to fixed screw terminal

#### Specifications

- max. voltage: 25V
- max. current: 4A
- max. operating temperature: 30°C

*All registered trademarks and trade names are properties of their respective owners and are used only for the clarification of the compatibility of our products with the products of the different manufacturers. Due to constant product improvements the actual product appearance might differ from the shown images. Product images are for illustrative purposes only.*

[REACH communication information according to article 33 WEEE](#)

- [velleman.eu](#)
- [hqpowers.eu](#)
- [parel.eu](#)
- [vellemanproject.com](#)  
EPC - modules - instruments
- [velbus.eu](#)
- [forum.velleman.eu](#)

#### Advertisements

