


Item no.: 2002-1401
 Product description: 4-CONDUCTOR THROUGH TERMINAL BLOCK; CENTRE-/LATERAL MARKING; suitable for Ex e II applications, 550V, 22 A; for DIN 35 rail; FRONT-ENTRY; CAGE CLAMP®S CONNECTION



Packing unit 100 pieces

Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Cross section from [mm ²]	0,25 mm ²
Cross section to [mm ²]	2,5 mm ²
Cross section from [AWG]	22 AWG
Cross section to [AWG]	12 AWG
Connection method	CONTACT CAGE CLAMP®CONNECTION
Cross section from [mm ²]	0,25 mm ²
Cross section to [mm ²]	4 mm ²
Cross section from [AWG]	22 AWG
Cross section to [AWG]	12 AWG
Wiring method	e+f
Connection method	CONTACT CAGE CLAMP®CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	24 A
Weight	6,688 g
Color	grey
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	1
Height	33 mm



Width	5,2 mm
Width	0,205 in
Depth	70 mm
Depth	2,76 in
Strip length from	10 mm
Strip length to	12 mm
Strip length	0,43 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
2002-1401	ABS	05-HG476175/1-PDA	800	24	0,5-4
2002-1401	AEX	E185892	550	20	22-12
2002-1401	CCA	NL6341	800	24	0,5-4
2002-1401	CSA	154112-1536069	600	20	22-12
2002-1401	cURus-EX	E185892	550	20	22-12
2002-1401	DNV	E7570	800	24	0,5-4
2002-1401	GL	26187-05HH	800	24	0,25-2,5
2002-1401	IECEX	IECEXPTB03.0004U	550	22	0,2-4
2002-1401	KEMA	NL2115558.01	800	24	0,5-4
2002-1401	LR	91/20112(E5)	800	24	0,5-4
2002-1401	PRS	TE/1718/880590/08	800	24	0,5-4
2002-1401	PRS	TE/1718/880590/08	800	24	0,5-4
2002-1401	PTB	PTB03A tex1162U	550	22	0,2-4
2002-1401	UL	E45172	600	20	22-12
2002-1401	UR	E45172	600	20	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected