


Item no.: 2006-1301  
 Product description: 3-CONDUCTOR THROUGH TERMINAL BLOCK; CENTRE-/ LATERAL MARKING; suitable for Ex e II applications at 550 V, 36 A; for DIN 35 rail; FRONT-ENTRY; CAGE CLAMP®S CONNECTION



Packing unit 25 pieces

Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Cross section from [mm <sup>2</sup> ]	0,5 mm <sup>2</sup>
Cross section to [mm <sup>2</sup> ]	6 mm <sup>2</sup>
Cross section from [AWG]	20 AWG
Cross section to [AWG]	8 AWG
Connection method	CONTACT CAGE CLAMP®CONNECTION
Cross section from [mm <sup>2</sup> ]	0,5 mm <sup>2</sup>
Cross section to [mm <sup>2</sup> ]	10 mm <sup>2</sup>
Cross section from [AWG]	20 AWG
Cross section to [AWG]	8 AWG
Wiring method	e+f
Connection method	CONTACT CAGE CLAMP®CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	41 A
Weight	11,845 g
Color	grey
Wiring type	Front-entry
No. of connection Points	3
No. of potentials	1
Height	33 mm



Width	7,5 mm
Width	0,295 in
Depth	73,5 mm
Depth	2,89 in
Strip length from	13 mm
Strip length to	15 mm
Strip length	0,55 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
2006-1301	ABS	05-HG476175/1-PDA	800	41	0,5-16
2006-1301	AEX	E185892	550	50	20-8
2006-1301	CCA	NL6342	800	41	0,5-10
2006-1301	CSA	154112-1543858	600	50	20-8
2006-1301	cURus-EX	E185892	550	50	20-8
2006-1301	DNV	E7570	800	41	0,5-10
2006-1301	GL	26187-05HH	800	41	0,5-6
2006-1301	IECEX	IECEXPTB05.0014U	550	33	0,5-10
2006-1301	KEMA	NL2115558.02	800	41	0,5-6
2006-1301	LR	91/20112(E5)	800	41	0,5-10
2006-1301	PRS	TE/1718/880590/08	800	41	0,5-10
2006-1301	PTB	PTB05Atex1030U	550	33	0,5-10
2006-1301	UL	E45172	600	50	20-8
2006-1301	UR	E45172	600	50	20-8

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected