


Item no.: 232-104/026-000  
 Product description: ANGLED FEMALE PLUG; 4 POLE; PIN SPACING 5 MM / 0.197 IN; WITH CODIG FINGERS; WITH INTEGRATED FIXING FLANGES; CONDUCTOR EXIT OPPOSITE TO LATCHES



Packing unit 100 pieces

Product group	3 (Multi Conn. System)
Pin spacing from	5 mm
Pin spacing from	0,197 in
pole count	4
Cross section from [mm <sup>2</sup> ]	0,08 mm <sup>2</sup>
Cross section to [mm <sup>2</sup> ]	2,5 mm <sup>2</sup>
Cross section from [AWG]	28 AWG
Cross section to [AWG]	12 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	250 V
Measured shock voltage	4 kV
Pollution degree	3
Current intensity EN	14 A
Weight	7,556 g
Color	grey
No. of connection Points	4
No. of potentials	4
Height	23,9 mm
Height	0,941 in
Width	22,4 mm
Width	0,882 in
Depth	22,75 mm



Depth	0,896 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0,33 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
232-104/026-000	ABS	04-HG469925-PDA	250	14	0,8-2,5
232-104/026-000	BV	11915/A0	400	16	2,5
232-104/026-000	CCA	5764	250	12	0,08-2,5
232-104/026-000	CSA	154112-1466354	300	15	22-12
232-104/026-000	DEMKO	88126	250		2,5
232-104/026-000	GL	17296-00HH	250	14	0,8-2,5
232-104/026-000	KEMA	2083746.02	250	12	0,08-2,5
232-104/026-000	KR	HMB05880-EL003	250/400	12/16	2,5
232-104/026-000	LR	96/20035	250	14	0,8-2,5
232-104/026-000	NEMKO	P94101840	250		2,5
232-104/026-000	RMR	11130002	250	14	0,8-2,5
232-104/026-000	UR	E45171	600	15	12
232-104/026-000	UR	E45172	300	15	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected