

Item no.: 261-301
 Product description: 2-CONDUCTOR TERMINAL BLOCK; LATERAL MARKING;
 WITH FIXING FLANGE; WITH MOUNTING FEET 209-123
 FOR TS 35; SIDE-ENTRY; CAGE CLAMP®CONNECTION



Packing unit 200 4*50 pieces

| | |
|--------------------------|---------------------------|
| Product group | 9 (Std Chassis Mt Blocks) |
| Cross section from [mm²] | 0,08 mm² |
| Cross section to [mm²] | 2,5 mm² |
| Cross section from [AWG] | 28 AWG |
| Cross section to [AWG] | 14 AWG |
| Connection method | CAGE CLAMP®CONNECTION |
| Measured voltage EN | 500 V |
| Measured shock voltage | 6 kV |
| Pollution degree | 3 |
| Current intensity EN | 24 A |
| Weight | 2,3 g |
| Color | grey |
| Wiring type | Side-entry |
| No. of connection Points | 2 |
| No. of potentials | 1 |
| Height | 18 mm |
| Height | 0,709 in |
| Width | 6 mm |
| Width | 0,236 in |
| Depth | 28 mm |
| Depth | 1,103 in |
| Strip length from | 8 mm |
| Strip length to | 9 mm |
| Strip length | 0,33 in |



| Item number | Admission office | Approval no. | Voltage [V] | Current [A] | Cross section [mm ²] |
|-------------|------------------|-------------------|-------------|-------------|-----------------------------------|
| 261-301 | ABS | 04-HG476174-PDA | 500 | 26 | 2,5 |
| 261-301 | BV | 07436/C0 | 500 | 24 | 0,08-2,5 |
| 261-301 | CCA | NL5801 | 500 | | 0,08-2,5 |
| 261-301 | CSA | 18677-45 | 300/600 | 20/5 | 26-14 |
| 261-301 | DNV | E7569 | 500 | 24 | 2,5 |
| 261-301 | GL | 17295-00HH | 500 | 24 | 2,5 |
| 261-301 | KEMA | 2079569.02 | 500 | | 0,08-2,5 |
| 261-301 | KR | HMB05880-EL002 | 500 | 24 | 2,5 |
| 261-301 | LR | 92/20242(E5) | 400 | 24 | 2,5 |
| 261-301 | PRS | TE/1718/880590/08 | 500 | | 0,08-2,5 |
| 261-301 | RMR | 11130002 | 500 | 26 | 2,5 |
| 261-301 | UR | E45172 | 300/600 | 15/5 | 28-14 |

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected