

Item no.: 261-331
 Product description: 4-CONDUCTOR TERMINAL BLOCK; LATERAL MARKING;
 WITH FIXING FLANGE; WITH MOUNTING FEET 209-123
 FOR TS 35; SIDE-ENTRY; CAGE CLAMP®CONNECTION



Packing unit 200 4*50 pieces

Product group	9 (Std Chassis Mt Blocks)
Cross section from [mm²]	0,08 mm²
Cross section to [mm²]	2,5 mm²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	14 AWG
Connection method	CAGE CLAMP®CONNECTION
Number of strands	2
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	24 A
Weight	3,81 g
Color	grey
Wiring type	Side-entry
No. of connection Points	4
No. of potentials	1
Height	18 mm
Height	0,709 in
Width	10 mm
Width	0,394 in
Depth	28 mm
Depth	1,103 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0,33 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
261-331	ABS	04-HG476174-PDA	500	26	2,5
261-331	BV	07436/C0	500	24	0,08-2,5
261-331	CCA	NL5801	500		0,08-2,5
261-331	CSA	18677-45	300/600	20/5	26-14
261-331	DEMKO	120039/02	500	24	2,5
261-331	Dep.MaE	CS4590N	300	27	
261-331	DNV	E7569	500	24	2,5
261-331	GL	17295-00HH	500	24	2,5
261-331	KEMA	2079569.02	500		0,08-2,5
261-331	KR	HMB05880-EL002	500	24	2,5
261-331	LR	92/20242(E4)	400	24	2,5
261-331	NEMKO	M59289/06	500		2,5
261-331	PRS	TE/1718/880590/08	500		0,08-2,5
261-331	RMR	11130002	500	26	2,5
261-331	SEMKO	9408057	500		2,5
261-331	UL	E45172	300/600	15/5	28-14
261-331	UR	E45172	300/600	15/5	28-14

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected