

Item no.: 264-351  
 Product description: 4-CONDUCTOR CENTRE TERMINAL BLOCK; CENTRE MARKING; FRONT-ENTRY; CAGE CLAMP®CONNECTION; HORIZONTAL TYPE



Packing unit 100 pieces

Product group	9 (Std Chassis Mt Blocks)
Cross section from [mm²]	0,08 mm²
Cross section to [mm²]	2,5 mm²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	12 AWG
Connection method	CAGE CLAMP®CONNECTION
Number of strands	2
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	24 A
Weight	6,24 g
Color	grey
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	1
Height	22 mm
Height	0,867 in
Width	10 mm
Width	0,394 in
Depth	32 mm
Depth	1,26 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0,33 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
264-351	ABS	04-HG476174-PDA	800	24	2,5
264-351	BBJ	B/12/696/03	800	24	2,5
264-351	BV	07436/C0			0,08-2,5
264-351	CSA	18677-23	600	20	26-12
264-351	DEMKO	120040/120039/04		24	2,5
264-351	DNV	E7569	800	24	2,5
264-351	GL	17295-00HH	800	24	2,5
264-351	KEMA	2079569.04	800		2,5
264-351	KR	HMB05880-EL002	800	24	
264-351	LR	92/20242(E4)	800	24	2,5
264-351	NEMKO	L94015	750		2,5
264-351	RMR	11130002	800	24	2,5
264-351	SEMKO	9404012			2,5
264-351	UL	E45172	600	20	28-12
264-351	UR	E45172	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected