

---

Item no.: 264-354  
Product description: 4-CONDUCTOR CENTRE TERMINAL BLOCK; CENTRE MARKING; SUITABLE FOR EX I APPLICATIONS; FRONT-ENTRY; CAGE CLAMP®CONNECTION; HORIZONTAL TYPE

---



Packing unit 100 pieces

|                                       |                           |
|---------------------------------------|---------------------------|
| Product group                         | 9 (Std Chassis Mt Blocks) |
| Cross section from [mm <sup>2</sup> ] | 0,08 mm <sup>2</sup>      |
| Cross section to [mm <sup>2</sup> ]   | 2,5 mm <sup>2</sup>       |
| Cross section from [AWG]              | 28 AWG                    |
| Cross section to [AWG]                | 12 AWG                    |
| Connection method                     | CAGE CLAMP®CONNECTION     |
| Number of strands                     | 2                         |
| Measured voltage EN                   | 800 V                     |
| Measured shock voltage                | 8 kV                      |
| Pollution degree                      | 3                         |
| Current intensity EN                  | 24 A                      |
| Weight                                | 6,25 g                    |
| Color                                 | blue                      |
| Wiring type                           | Front-entry               |
| No. of connection Points              | 4                         |
| No. of potentials                     | 1                         |
| Height                                | 22 mm                     |
| Height                                | 0,867 in                  |
| Width                                 | 10 mm                     |
| Width                                 | 0,394 in                  |
| Depth                                 | 32 mm                     |
| Depth                                 | 1,26 in                   |



|                   |         |
|-------------------|---------|
| Strip length from | 8 mm    |
| Strip length to   | 9 mm    |
| Strip length      | 0,33 in |



| Item number | Admission office | Approval no.    | Voltage [V] | Current [A] | Cross section [ mm <sup>2</sup> ] |
|-------------|------------------|-----------------|-------------|-------------|-----------------------------------|
| 264-354     | ABS              | 04-HG476174-PDA | 800         | 24          | 2,5                               |
| 264-354     | BV               | 07436/C0        |             |             | 0,08-2,5                          |
| 264-354     | CSA              | 18677-23        | 600         | 20          | 26-12                             |
| 264-354     | DNV              | E7569           | 800         | 24          | 2,5                               |
| 264-354     | GL               | 17295-00HH      | 800         | 24          | 2,5                               |
| 264-354     | KEMA             | 2079569.04      | 800         |             | 2,5                               |
| 264-354     | KR               | HMB05880-EL002  | 800         | 24          |                                   |
| 264-354     | LR               | 92/20242(E5)    | 800         | 24          | 2,5                               |
| 264-354     | RMR              | 11130002        | 800         | 24          | 2,5                               |
| 264-354     | UR               | E45172          | 600         | 20          | 28-12                             |

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected