

Item no.: 280-621
 Product description: 4-CONDUCTOR THROUGH TERMINAL BLOCK; LATERAL MARKING; for DIN 35 rail; FRONT-ENTRY; CAGE CLAMP®CONNECTION; HORIZONTAL TYPE



Packing unit 100 pieces

Product group	1 (Rail Mounted Terminal Blocks)
Cross section from [mm ²]	0,08 mm ²
Cross section to [mm ²]	2,5 mm ²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	12 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	24 A
Weight	8,4 g
Color	grey
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	1
Height	28 mm
Height	1,1 in
Width	5 mm
Width	0,197 in
Depth	73 mm
Depth	2,87 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0,33 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
280-621	ABS	05-HG476175/1-PDA	800	24	2,5
280-621	BBJ	B/12/700/03	800	24	2,5
280-621	BV	07436/C0			0,08-2,5
280-621	CCA	NL5855	800		2,5
280-621	CSA	154112-1536071	600	15	28-14
280-621	DEMKO	78571	750		2,5
280-621	Dep.MaE	CS4865N	600	25	2,5
280-621	DNV	E7570	800	20	2,5
280-621	GL	17295-00HH	800	24	2,5
280-621	KEMA	2082859.07	800		2,5
280-621	LR	91/20112(E5)	800	24	2,5
280-621	PRS	TE/1718/880590/08	800		2,5
280-621	RMR	11130002	800	24	2,5
280-621	SABS	751/82640	750		2,5
280-621	UR	E45172	600	15	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected