

Item no.: 281-620
 Product description: DOUBLE DECK TERMINAL BLOCK; CENTRE MARKING;
 WITH HORIZONTAL JUMPERING ON LOWER LEVEL;
 THROUGH/THROUGH; for DIN 35 rail; FRONT-ENTRY



Packing unit 50 pieces

Product group	1 (Rail Mounted Terminal Blocks)
Number of levels	2
Cross section from [mm ²]	0,08 mm ²
Cross section to [mm ²]	4 mm ²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	12 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	26 A
Weight	15,682 g
Color	grey
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	2
Height	58,5 mm
Height	2,3 in
Width	6 mm
Width	0,236 in
Depth	83,5 mm
Depth	3,29 in



Strip length from	9 mm
Strip length to	10 mm
Strip length	0,37 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
281-620	ABS	05-HG476175/1-PDA	500	26	4,0
281-620	BV	07436/Co	500	26	4,0
281-620	CCA	NL5591/1	500	26	4
281-620	CSA	154112-1505034	600	25	28-12
281-620	DEMKO	75942	750		4
281-620	DNV	E7570	800	32	4,0
281-620	GL	17295-00HH	500	26	4
281-620	KEMA	2076376.01	500	26	4
281-620	KR	HMB05880-EL001	500/800	10/35	4
281-620	LR	91/20112(E5)	500	26	4,0
281-620	PRS	TE/1718/880590/08	500	26	4
281-620	RMR	11130002	500	26	4,0
281-620	UR	E45172	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected