
Item no.: 281-657
Product description: 4-CONDUCTOR EARTH TERMINAL BLOCK; CENTRE MARKING; for DIN 35 rail; FRONT-ENTRY; CAGE CLAMP®CONNECTION; HORIZONTAL TYPE



Packing unit 50 pieces

Product group	1 (Rail Mounted Terminal Blocks)
Cross section from [mm ²]	0,08 mm ²
Cross section to [mm ²]	4 mm ²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	12 AWG
Connection method	CAGE CLAMP®CONNECTION
Weight	17,298 g
Color	green-yellow
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	1
Height	29 mm
Height	1,14 in
Width	6 mm
Width	0,236 in
Depth	86 mm
Depth	3,39 in
Strip length from	9 mm
Strip length to	10 mm
Strip length	0,37 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
281-657	ABS	05-HG476175/1-PDA			4,0
281-657	AEX	E185892			28-12
281-657	BBJ	B/12/700/03			4,0
281-657	BV	07436/C0			0,08-4
281-657	BV	07436/Co	250	6,3	4,0
281-657	CCA	NL5591/1			4
281-657	CSA	154112-1505034			28-12
281-657	cURus-EX	E185892			28-12
281-657	DEMKO	113344			4
281-657	Dep.MaE	CS4866N	600	25	4
281-657	DNV	E7570			4,0
281-657	GL	17295-00HH			4
281-657	KEMA	2076376.01			4
281-657	KR	HMB05880-EL001	500/800	10/35	4
281-657	LR	91/20112(E5)	250	6,3	4,0
281-657	NEMKO	L92062			4
281-657	PRS	TE/1718/880590/08			4
281-657	RMR	11130002	250	6,3	4,0
281-657	UR	E45172			28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected