

---

Item no.: 281-679  
Product description: 3-CONDUCTOR THROUGH TERMINAL BLOCK

---



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm <sup>2</sup> ]	0.08 - 4 mm <sup>2</sup>
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	32 A
Weight	11.003 g
Color	red
Wiring type	Front-entry
No. of connection Points	3
No. of potentials	1
Height	29 mm
Height	1.14 in
Width	6 mm
Width	0.236 in
Depth	73.5 mm
Depth	2.89 in

Strip length from  
Strip length to  
Strip length  
Mounting

9 mm  
10 mm  
0.37 in  
TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
281-679	ABS	05-HG476175/3-PDA	800	32	4,0
281-679	BV	07436/C0	800	32	4,0
281-679	CCA	NL5591/1	800	32	4
281-679	CSA	154112-1505034	600	25	28-12
281-679	DNV	E-10423	800	32	4,0
281-679	GL	17295-00HH	800	32	4
281-679	KEMA	2076376.01	800	32	4
281-679	LR	91/20112(E6)	800	32	4,0
281-679	PRS	TE/1718/880590/08	800	32	4
281-679	RMR	11130002	800	32	4,0
281-679	UR	E45172	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected