

---

Item no.: 281-687  
Product description: 3-CONDUCTOR EARTH TERMINAL BLOCK; CENTRE MARKING; for DIN 35 rail; FRONT-ENTRY; CAGE CLAMP®CONNECTION; HORIZONTAL TYPE

---



Packing unit 50 pieces

Product group	1 (Rail Mounted Terminal Blocks)
Cross section from [mm <sup>2</sup> ]	0,08 mm <sup>2</sup>
Cross section to [mm <sup>2</sup> ]	4 mm <sup>2</sup>
Cross section from [AWG]	28 AWG
Cross section to [AWG]	12 AWG
Connection method	CAGE CLAMP®CONNECTION
Weight	15,973 g
Color	green-yellow
Wiring type	Front-entry
No. of connection Points	3
No. of potentials	1
Height	29 mm
Height	1,14 in
Width	6 mm
Width	0,236 in
Depth	73,5 mm
Depth	2,89 in
Strip length from	9 mm
Strip length to	10 mm
Strip length	0,37 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
281-687	ABS	05-HG476175/1-PDA			4,0
281-687	AEX	E185892			28-12
281-687	BBJ	B/12/700/03			4,0
281-687	BV	07436/Co	800	32	4,0
281-687	CCA	NL5591/1			4
281-687	CSA	154112-1505034			28-12
281-687	cURus-EX	E185892			28-12
281-687	DEMKO	75942	750		4
281-687	Dep.MaE	CS4866N	600	25	4
281-687	DNV	E7570			4,0
281-687	GL	17295-00HH			4
281-687	KEMA	2076376.01			4
281-687	KR	HMB05880-EL001	500/800	10/35	4
281-687	LR	91/20112(E5)	800	32	4,0
281-687	PRS	TE/1718/880590/08			4
281-687	RMR	11130002	800	32	4,0
281-687	UR	E45172			28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected