
Item no.: 285-601
Product description: 2-CONDUCTOR THROUGH TERMINAL BLOCK; LATERAL MARKING; for DIN 35 rail; FRONT-ENTRY; CAGE CLAMP®CONNECTION; HORIZONTAL TYPE



Packing unit 15 pieces

Product group	1 (Rail Mounted Terminal Blocks)
Cross section from [mm ²]	6 mm ²
Cross section to [mm ²]	35 mm ²
Cross section from [AWG]	10 AWG
Cross section to [AWG]	2 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	125 A
Weight	131,446 g
Color	grey
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	52,5 mm
Height	2,07 in
Width	16 mm
Width	0,63 in
Depth	115,5 mm
Depth	4,55 in
Strip length from	23 mm



Strip length	0,91 in
Strip length from	16 mm
Strip length to	16 mm
Strip length	0,63 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
285-601	ABS	05-HG476175/1-PDA	800	125	35,0
285-601	BBJ	B/12/700/03	800	125	35,0
285-601	BV	07436/C0			6-35
285-601	CCA	NL5643	800	125	35
285-601	CSA	154112-1327714	600	140	8-2
285-601	DNV	E7570	800	125	35,0
285-601	GL	17295-00HH	800	125	35
285-601	KEMA	2076789.01	800	125	35
285-601	KR	HMB05880-EL001	800	138	35,0
285-601	LR	91/20112(E5)	800	125	35,0
285-601	PRS	TE/1718/880590/08	800	125	35
285-601	RMR	11130002	800	125	35,0
285-601	UL	E45172	600	115	10-2
285-601	UR	E45172	600	115	10-2

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected