

Data

Technical Data

Rated current	10 A
---------------	------

Connection data

Solid conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
-----------------	--

Strip length	9 ... 10 mm / 0.35 ... 0.39 inch
--------------	----------------------------------

Geometrical Data

Width	12 mm / 0.472 inch
-------	--------------------

Depth	74.3 mm / 2.925 inch
-------	----------------------

Mechanical data

Pluggable connector	yes
---------------------	-----

Material Data

Color	light gray
-------	------------

Fire load	0.204 MJ
-----------	----------

Weight	11.229 g
--------	----------

Environmental Requirements

Surrounding air (operating) temperature	0 ... 55 °C
---	-------------







Surrounding air (storage) temperature	-25 ... 85 °C
Protection class	IP20

Commercial data


Product Group	15 (Remote I/O)
Country of origin	CN
GTIN	4050821043928
Customs Tariff No.	85366990990

Approvals / Certificates

Ship Approvals

Logo	Approval	Additional Approval Text	Certificate name
	ABS American Bureau of Shipping	-	19- HG1821926
	DNV GL Det Norske Veritas, Germanischer Lloyd	-	TAA0000194
	KR Korean Register of Shipping	-	HMB05880- AC001
	LR Lloyds Register	-	02/20026 (E6)
	PRS Polski Rejestr Statków	-	TE/2236 /880590/19
	RINA RINA Germany GmbH	-	ELE066419XG

UL-Approvals

Logo	Approval	Additional Approval Text	Certificate name
	cURus Underwriters Laboratories Inc.	UL 1059	E45172



Downloads

Documentation

Bid Text

753-110	Apr 4, 2012	doc	Download
IO, Zubehoer		22.5 kB	

CAD/CAE-Data

CAD data

3D Download 753-110	URL	Download
---------------------	-----	----------

WSCAD

WSCAD Universe 753-110	Download
------------------------	----------

Product family

750/753 Series I/O-System

[Show all products from the family](#)

Subject to changes.